

PRODUCT SPECIFICATION

HandPRO[®] **SERIES 1550** **CLEAN CLASS VINYL GLOVES**

300mm (12") Length

ISO Class 5 Compatible

Clear Vinyl

Smooth

Powder-Free

Ambidextrous

Non-Sterile

Beaded Cuff



CE
EN420

EN 374-1:2003



EN 374-2:2003



Level 1

QUALITY & CONFORMITY

- Manufactured in an ISO 9001:2008 certified facility
- Conforms to Council Directive 89/686/EEC
- Complies with European Standards EN374 Parts 1/2/3, and EN420 concerning Category I “Glove of Simple Design - For Minimal Risk Only”
- Complies with FDA CFR 21 177.2600 for food handling
- Conforms to the following additional test standards:

IEST-RP-CC005.4	Recommended Practice for Cleanroom Gloves
ASTM D5151-99	Standard Test for Detection of Holes in Medical Gloves
ASTM D5250-06	Standard Specification for Poly(vinyl chloride) Gloves

PERFORMANCE REQUIREMENTS

Characteristic	Inspection Level	AQL
Freedom from Holes	G1	4.0
Visual Defects (Major)	G1	1.5
Visual Defects (Minor)	G1	1.5
Physical Properties	S2	4.0
Physical Dimensions	S2	4.0
Powder Residue	N=3	<2mg/glove

PHYSICAL DIMENSIONS

Size	Small (6/7)	Medium (7/8)	Large (8/9)	X-Large (9/10)
Palm Width ± 3 mm	85	95	105	115
Glove Length (mm)	300 \pm 10			
Thickness (mm)	Manufacturing Minimum			
Cuff	0.06 \pm 0.01			
Palm (center of palm)	0.08 \pm 0.01			
Finger (13 \pm 3 mm from tip)	0.11 \pm 0.03			

PHYSICAL PROPERTIES

Test	After Aging Manufacturing Minimum
Tensile Strength (MPa)	11
Ultimate Elongation	300%

The specifications provided reflect the minimum acceptable requirements of the ASTM and FDA where applicable. Actual testing results are available upon request. Gloves offered by Hourglass International, Inc. meet or exceed these physical requirements. Independent laboratory test results are available upon request.

Your Protection Is
Our Purpose



- Hourglass-Intl.com
- (800) 277-0994
- hourglass-international-inc
- hourglassinternationalinc
- HourglassIntl

USA

ESD PROPERTIES

HandPRO 1550 is a Static Dissipative Vinyl Glove

PRODUCT NUMBERS

Size	Item #	Case Quantity
Small	1551	1000
Medium	1552	1000
Large	1553	1000
X-Large	1554	1000

PACKAGING

A 50 glove stack is placed into the right side of a plain bag, and another 50 gloves are placed on the left side of the same plain bag. The plain bag is sealed and placed into another outer bag. The outer bag is sealed. Ten packed outer bags are placed into a carton box with a carton liner. Carton liners are twist tie wrapped and carton is sealed with transparent tape. Outer bags and cartons are stamped with a lot number.

SHELF LIFE & STORAGE

Five years from date of manufacture. Store in a cool, dry place away from direct sunlight.

Manufactured in China for Hourglass International, Inc.

The information on this document is a guideline of typical values and characteristics of the product.